



# UV-B Narrowband PL-L/PL-S

## PL-S 9W/01/2P 1CT/6X10BOX

Philips offers highly reliable PL-L & PL-S lamps with narrow waveband of between 305 and 315 nm which peaks at 311 nm. This makes these lamps suitable for various applications such as phototherapy, agriculture & curing.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G23 [G23]
Life to 50% Failures (Nom)	1,000 hour(s)
Useful Life (Nom)	1,000 hour(s)

Light Technical	
Color Code	01
Color Designation	Ultra Violet B
UV Depreciation at 1000 h	20 %
UV Depreciation at 500 h	15 %

Operating and Electrical	
Power Consumption	8.6 W
Lamp Current (Nom)	0.17 A
Voltage (Nom)	60 V
Voltage (Nom)	60 V

Mechanical and Housing	
Bulb Shape	2XT12

Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg

UV	
UV-B Radiation 100 hr (IEC)	1.0 W
UV-B Radiation 5hr (IEC)	1.2 W


  

Product Data	
Order product name	PL-S 9W/01/2P 1CT/6X10BOX
Full product name	PL-S 9W/01/2P 1CT/6X10BOX
Full product code	871869666110900
Order code	323287
Material Nr. (12NC)	927901700151
Numerator - Quantity Per Pack	1

## UV-B Narrowband PL-L/PL-S


EAN/UPC - Product/Case	8718696661109
Numerator - Packs per outer box	60
EAN/UPC - Case	8718696661123

### Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-S 9W/01/2P 1CT/6X10BOX	13 mm	28 mm	129 mm	144.5 mm	167 mm

### Photometric data



Spectral Power Distribution Colour - PL-S 9W/01/2P 1CT/6X10BOX

