



# Actinic BL PL-S/PL-L

## PL-S 9W/10/2P Lead Free

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Product data


General Information	
Base	G23 [ G23]
Main Application	Insect traps
Life to 50% Failures (Nom)	1000 h
Useful Life (Nom)	2000 h
Light Technical	
Color Code	210 [ leadfree 360 glass (10)]
Color Designation	Ultra Violet A
Chromaticity Coordinate X (Nom)	227
Chromaticity Coordinate Y (Nom)	212
UV Depreciation at 2000 h	20 %
Operating and Electrical	
Power (Rated) (Nom)	8.6 W
Lamp Current (Nom)	0.17 A
Voltage (Nom)	60 V

Mechanical and Housing	
Cap-Base Information	2 Pins (2P)
UV	
UV-B/UV-A (IEC)	0.1 %
UV-A Radiation 100Hr (IEC)	1.66 W
Product Data	
Order product name	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX
EAN/UPC - Product	8711500951946
Order code	157651
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	927901721008
Net Weight (Piece)	32.000 g

### Warnings and Safety

# Actinic BL PL-S/PL-L


## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	13 mm	28 mm	128.8 mm	144.5 mm	167 mm

PL-S 9W/210/2P

## Photometric data



XDPO\_XUAPLS\_10\_110\_210-Spectral power distribution Colour

