



PL-S Short 2-Pin Base

PL-S 13W/850/2P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

General Information	
Base	GX23 [GX23]
Life To 10% Failures (Nom)	0 h
Life to 50% Failures (Nom)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	95 %
LSF 8000 h Rated	86 %
Light Technical	
Color Code	850 [CCT of 5000K]
Initial lumen (Nom)	810 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	94 %
LLMF 4000 h Rated	91 %
LLMF 6000 h Rated	89 %
LLMF 8000 h Rated	86 %

Operating and Electrical	
Power (Rated) (Nom)	13 W
Lamp Current (Nom)	0.290 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap-Base Information	2P
Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-S 13W/850/2P/ALTO
EAN/UPC - Product	046677146870
Order code	146878


PL-S Short 2-Pin Base

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927902785021
Net Weight (Piece)	35.000 g

ILCOS Code	FSD-13/50/1B-I-GX23
------------	---------------------

Warnings and Safety

Dimensional drawing




Product


PL-S 13W/850/2P/ALTO

PL-S ALTO 13W/850/2P

Lifetime



LDLE_PLS2PLM_0002-Life expectancy diagram



PL-S Short 2-Pin Base

