



Actinic BL PL-S/PL-L

PL-L18W/10

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	2G11
Life to 50% Failures (Nom)	15,000 hour(s)
Useful Life (Nom)	5,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Ultra Violet A
Chromaticity Coordinate X (Nom)	228
Chromaticity Coordinate Y (Nom)	215
UV Depreciation at 2000 h	20 %


UV Depreciation at 5000 h	35 %
Operating and Electrical	
Power Consumption	18 W
Lamp Current (Nom)	0.375 A
Voltage (Nom)	58 V
Voltage (Nom)	58 V
Mechanical and Housing	
Bulb Shape	2xT16

Actinic BL PL-S/PL-L

UV	
UV-A Radiation 100Hr (IEC)	3.5 W
Product Data	
Order product name	PL-L 18W/10/4P 1CT/25
Full product name	PL-L18W/10
Full product code	871150026018540
Order code	130344


Material Nr. (12NC)	927903001007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260185
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500260192

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 18W/10/4P 1CT/25	3/4 inch	1-9/16 inch	7-11/16 inch	8-11/16 inch	8-15/16 inch

Photometric data



Spectral Power Distribution Colour - PL-L 18W/10/4P 1CT/25

