



# **UV-B Narrowband PL-L/PL-S**

## PL-L 36W/01/4P 1CT/25

More than 400 independent clinical studies have proven that the UVB Narrowband PL-L/PL-S lamps are safer and more effective than any other lamps in their class. The PL-L/PL-S versions provide additional design freedom for system manufacturers since these are space-saving compact, single-ended lamps. Further flexibility is assured since they use the same lamp caps as general lighting lamps, they also use the same universal ballasts. Their best-in-class treatment effectiveness is a result of their very narrow waveband emission: between 305 and 315 nm with a peak at 311 nm. This is the most efficacious waveband for the treatment of psoriasis, and is therefore much more focused. As a result, exposure times are much shorter and this in turn leads to a reduction of side effects such as reddening of the skin and itching. All of this makes them ideal for phototherapy treatment of diseases such as psoriasis and vitiligo. What's more, because the overall dosage of this narrowband radiation can be closely controlled, these lamps are suitable for home therapy.

### **Warnings and Safety**

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### **Product data**

General Information		Useful Life (Nom)	1,000 hour(s)
Cap-Base	2G11 [2G11]		


Datasheet, 2023, April 15 data subject to change

# **UV-B Narrowband PL-L/PL-S**

Light Technical		
Color Code	01	
Chromaticity Coordinate X (Nom)	224	
Chromaticity Coordinate Y (Nom)	228	
UV Depreciation at 1000 h	20 %	
UV Depreciation at 500 h	15 %	
Operating and Electrical		
Power Consumption	36 W	
Lamp Current (Nom)	0.435 A	
Voltage (Nom)	105 V	
Voltage (Nom)	105 V	
Mechanical and Housing		
Bulb Shape	2xT16	
Approval and Application		
Mercury (Hg) Content (Nom)	4.4 mg	


JV			
JV-B Radiation 100 hr (IEC)	4.8 W		
JV-B Radiation 5hr (IEC)	6.2 W		
No doct Date			
Product Data			
order product name	PL-L 36W/01/4P 1CT/25		
ull product name	PL-L 36W/01/4P 1CT/25		
ull product code	871150086889340		
Order code	927903400121		
laterial Nr. (12NC)	927903400121		
lumerator - Quantity Per Pack	1		
AN/UPC - Product/Case	8711500868893		
lumerator - Packs per outer box	25		
AN/UPC - Case	8711500868909		

## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 36W/01/4P 1CT/25	18 mm	39 mm	384.2 mm	410 mm	416.6 mm

## Photometric data



Spectral Power Distribution Colour - PL-L 36W/01/4P 1CT/25

# **UV-B Narrowband PL-L/PL-S**



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.