



Actinic BL PL-S/PL-L

PL-L 36W/10/4P 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Product data

General Information	
Base	2G11 [2G11]
Main Application	Insect traps
Life to 50% Failures (Nom)	11000 h

Light Technical	
Color Code	210 [leadfree 360 glass (10)]
Chromaticity Coordinate X (Nom)	220
Chromaticity Coordinate Y (Nom)	215
UV Depreciation at 2000 h	15 %
UV Depreciation at 5000 h	20 %

Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp Current (Nom)	0.435 A
Voltage (Nom)	106 V

Mechanical and Housing	
Cap-Base Information	4 Pins (4P)

Approval and Application	
Mercury (Hg) Content (Max)	2.1 mg
Mercury (Hg) Content (Nom)	2.0 mg


UV	
UV-A Radiation 100Hr (IEC)	8.5 W

Product Data	
XUCDM.COPY.Product.Title	PL-L 36W/10/4P 1CT/25
EAN/UPC - Product	8711500264817
Order code	232934
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927903421007
Net Weight (Piece)	104.000 g

Actinic BL PL-S/PL-L

Warnings and Safety



Dimensional drawing



PL-L 36W/210/4P

Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 36W/10/4P ICT/25	18 mm	39 mm	384.2 mm	410 mm	416.6 mm

Photometric data



XDPO_XURPLL_0001-Spectral power distribution Colour

