



# MASTER PL-C 4 Pin

## MASTER PL-C 18W/827/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

### Product data

General Information	
Cap-Base	G24Q-2 [ G24q-2]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	1200 lm
Luminous Flux (Rated) (Nom)	1200 lm
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %

Operating and Electrical	
Power (Rated) (Nom)	16.5 W
Lamp Current (Nom)	0.230 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Full product code	871150062327070
Order product name	MASTER PL-C 18W/827/4P 1CT/5X10BOX


# MASTER PL-C 4 Pin

EAN/UPC - Product	8711500623270
Order code	927907282740
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	927907282740

Net Weight (Piece)	55.300 g
ILCOS Code	FSQ-18/27/1B-E-G24q=2

## Warnings and Safety

## Dimensional drawing




PL-C 18W/827/4P


## Product

MASTER PL-C 18W/827/4P 1CT/5X10BOX

## Photometric data



Lightcolor /827



Lightcolor /827

# MASTER PL-C 4 Pin

## Lifetime



### Life Expectancy 3 h cycle

### Life Expectancy 12 h cycle



### Lumen Maintenance 3 h and 12 h cycle

