# Lighting

**PHILIPS** 

### MASTER PL-L Xtra Polar 4 Pin

#### MASTER PL-L XTRA POLAR 36W/830/4P 1CT/25

MASTER PL-L Xtra Polar is a medium to high-wattage linear compact fluorescent lamp, typically used for lower-temperature applications such as outdoor lighting and cold storage. MASTER PL-L Xtra Polar lamps furthermore provide significantly lower operating costs thanks to their lifetime, which is more than double that of a standard MASTER PL-L lamp, and their very low early failure rate. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as HF electronic gear and is provided with a plug-in/pull-out lamp base.

#### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- · Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### **Product data**


tion		Colour designation	Warm White (WW)
	2G11 [2G11]	Chromaticity Coordinate X (Nom)	0.44
nent reference	Sphere	Chromaticity Coordinate Y (Nom)	0.403
Life to 50% failures (nom.)	21,000 h	Correlated Colour Temperature	3000 K
		Luminous efficacy (rated) (nom.)	81 lm/W
echnical		Colour rendering index (CRI)	82
Code	830 [CCT of 3000K]		
nous Flux	2,800 lm		

#### MASTER PL-L Xtra Polar 4 Pin

Operating and Electrical		
Power Consumption	36.3 W	
Lamp current (nom.)	0.445 A	
Controls and Dimming		
Dimmable	Yes	
Approval and Application		
Energy Efficiency Class	G	
Mercury (Hg) content (max.)	3 mg	
Mercury (Hg) content (nom.)	3.0 mg	
Energy consumption kWh/1,000 hours 37 kWh		
EPREL registration number	423310	


Product Data		
Order product name	MASTER PL-L XTRA POLAR 36W/830/4P	
	1CT/25	
Full product name	MASTER PL-L XTRA POLAR 36W/830/4P	
	1CT/25	
Full EOC	871150026776440	
Order code	26776440	
Material no. (12 NC)	927907783015	
SAP numerator - quantity per pack	1	
EAN/UPC — Product/Case	8711500267764	
Numerator – packs per outer box	25	
EAN/UPC - Case	8711500267771	

#### Dimensional drawing



## ProductD (max)D (max)A (max)B (max)C (max)MASTER PL-LXTRA POLAR 36W/39.0 mm18.0 mm343.2 mm410 mm416.6 mm830/4P 1CT/254 mm4 mm4 mm4 mm4 mm

#### Photometric data



Spectral Power Distribution Colour - MASTER PL-L XTRA POLAR 36W/830/4P 1CT/25

#### MASTER PL-L Xtra Polar 4 Pin



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 15 - data subject to change