



Actinic BL PL-L Secura

PL-L 36W/10/4P Secura 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL PL-L Secura lamps are perfect for attracting insects. With the compact PL-L product format in a variety of wattages, new attractive designs are possible. Furthermore, these lamps have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Product data

General Information		Voltage (Nom)	
Base	2G11 [2G11]	108 V	
Main Application	Insect traps	Mechanical and Housing	
Life to 50% Failures (Nom)	10000 h	Cap-Base Information	4 Pins (4P)
Light Technical		Approval and Application	
Color Code	10	Mercury (Hg) Content (Max)	2.0 mg
Chromaticity Coordinate X (Nom)	228	Mercury (Hg) Content (Nom)	1.8 mg
Chromaticity Coordinate Y (Nom)	215	UV	
UV Depreciation at 2000 h	20 %	UV-A Radiation 100Hr (IEC)	7.7 W
UV Depreciation at 5000 h	40 %	Product Data	
Operating and Electrical		Order product name	PL-L 36W/10/4P SECURA 1CT/25
Power (Rated) (Nom)	36 W	EAN/UPC - Product	8718291194439
Lamp Current (Nom)	0.440 A	Order code	285049


Actinic BL PL-L Secura

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927909121001

Net Weight (Piece)	133.000 g
--------------------	-----------

Warnings and Safety


Dimensional drawing



PL-L 36W/10/4P SECURA

Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
PL-L 36W/10/4P	27 mm	40 mm	20.0	404.2 mm	430.0 mm	436.6 mm
SECURA 1CT/25			mm			

Photometric data



XDPO_XURPLL_0001-Spectral power distribution Colour

