



# MASTER PL-R Eco 4 Pin



## MASTER PL-R ECO 14W/830/4P 1CT/5X10BOX

MASTER PL-R Eco is an extremely efficient compact fluorescent lamp for downlight applications. It consists of six parallel tubes with a new innovative 'twist and lock' lamp base, designed for operation with electronic gear. The MASTER PL-R Eco contains the original bridge technology invented and patented by Philips. This guarantees optimum performance in the application and results in significantly higher efficacies than with regular compact fluorescent lamps. On top of that, MASTER PL-R Eco lamps offer more than double the service life of a standard compact fluorescent lamp, thanks to superior lumen maintenance. The 'twist and lock' lamp base provides easy and safe (dis-)mounting and sturdy fixation in the luminaire.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Colour designation	
Cap base	GR14Q-1 [GR14q-1]	Warm White (WW)	
Flux measurement reference	Sphere	Chromaticity Coordinate X (Nom)	0.44
		Chromaticity Coordinate Y (Nom)	0.403
		Correlated Colour Temperature	3000 K
		Luminous efficacy (rated) (nom.)	72 lm/W
		Colour rendering index (CRI)	82
Light Technical			
Colour Code	830 [CCT of 3000K]		
Luminous Flux	1,000 lm		

MASTER PL-R Eco 4 Pin

Operating and Electrical	
Power Consumption	14.7 W
Lamp current (nom.)	0.150 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	15 kWh
EPREL registration number	423320


Product Data	
Order product name	MASTER PL-R Eco 14W/830/4P 1CT/5X10BOX
Full product name	MASTER PL-R ECO 14W/830/4P 1CT/5X10BOX
Full EOC	871150026595170
Order code	26595170
Material no. (12 NC)	927909983050
Local order code	14PLR830ECO
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500265951
Numerator – packs per outer box	50
EAN/UPC - Case	8711500265975

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-R Eco 14W/830/4P 1CT/5X10BOX	41.0 mm	99.7 mm	120.0 mm	126.6 mm



Photometric data




Spectral Power Distribution Colour - MASTER PL-R Eco 14W/830/4P 1CT/5X10BOX

MASTER PL-R Eco 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-R Eco 14W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-R Eco 14W/830/4P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-R Eco 14W/830/4P 1CT/5X10BOX

