



MASTER PL-R Eco 4 Pin



MASTER PL-R ECO 17W/830/4P 1CT/5X10BOX

MASTER PL-R Eco is an extremely efficient compact fluorescent lamp for downlight applications. It consists of six parallel tubes with a new innovative 'twist and lock' lamp base, designed for operation with electronic gear. The MASTER PL-R Eco contains the original bridge technology invented and patented by Philips. This guarantees optimum performance in the application and results in significantly higher efficacies than with regular compact fluorescent lamps. On top of that, MASTER PL-R Eco lamps offer more than double the service life of a standard compact fluorescent lamp, thanks to superior lumen maintenance. The 'twist and lock' lamp base provides easy and safe (dis-)mounting and sturdy fixation in the luminaire.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- $\boldsymbol{\cdot}$ Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information			
Cap base	GR14Q-1 [GR14q-1]		
Flux measurement reference	Sphere		
Light Technical			
Colour Code	830 [CCT of 3000K]		
Luminous Flux	1,150 lm		

Colour designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	0.44		
Chromaticity Coordinate Y (Nom)	0.403		
Correlated Colour Temperature	3000 K		
Luminous efficacy (rated) (nom.)	70 lm/W		
Colour rendering index (CRI)	82		


Datasheet, 2023, April 17 data subject to change

MASTER PL-R Eco 4 Pin

Operating and Electrical	
Power Consumption	17.7 W
Lamp current (nom.)	0.150 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	18 kWh
EPREL registration number	423322


Product Data				
Order product name	MASTER PL-R Eco 17W/830/4P 1CT/5X10BOX			
Full product name	MASTER PL-R ECO 17W/830/4P 1CT/5X10BO			
Full EOC	871150026601970			
Order code	26601970			
Material no. (12 NC)	927910083050			
Local order code	17PLR830ECO			
SAP numerator – quantity per pack	1			
EAN/UPC — Product/Case	8711500266019			
Numerator – packs per outer box	50			
EAN/UPC - Case	8711500266033			

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER DI -P Eco 17W/830/AD 1CT/5Y10BOY	41 0 mm	121.7 mm	1/12 () mm	1/18 6 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-R Eco 17W/830/4P 1CT/5X10BOX

MASTER PL-R Eco 4 Pin


Lifetime





Life Expectancy Diagram - MASTER PL-R Eco 17W/830/4P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-R Eco 17W/830/4P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-R Eco 17W/830/4P 1CT/ 5X10BOX



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.