



# TL-D LIFEMAX Super 80 JIS

## TL-D 18W/830 JIS 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires. The lamp is complying with Japanese Industrial Standard.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,450 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	80.5 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	18 W
Lamp Current (Nom)	0.35 A
Voltage (Nom)	65 V
Voltage (Nom)	65 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	TL-D 18W/830 JIS 1SL/25
Full product name	TL-D 18W/830 JIS 1SL/25
Full product code	871150028466200
Order code	927919983033
Material Nr. (12NC)	927919983033
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500284662
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500284679

TL-D LIFEMAX Super 80 JIS

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/830 JIS 1SL/25	28 mm	581.3 mm	588.4 mm	585.8 mm	595.5 mm

