



# MASTER TL-D Super 80

## MASTER TL-D Super 80 58W/830 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	59.4 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.670 A
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	5,240 lm		
Color Designation	Warm White (WW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.44	Bulb Shape	T8
Chromaticity Coordinate Y (Nom)	0.403		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	90 lm/W	Energy Efficiency Class	G
Color rendering index (CRI)	82	Mercury (Hg) Content (Nom)	1.7 mg
		Energy Consumption kWh/1000 h	60 kWh
		EPREL Registration Number	423394

# MASTER TL-D Super 80

Product Data	
Order product name	MASTER TL-D Super 80 58W/830 1SL/25
Full product name	MASTER TL-D Super 80 58W/830 1SL/25
Full product code	871150063213540
Order code	927922083023
Material Nr. (12NC)	927922083023
Local order code	9279-220-83023


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500632135
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500632142

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 58W/830 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL-D Super 80 58W/830 1SL/25

## Lifetime



Life Expectancy Diagram - MASTER TL-D Super 80 58W/830 1SL/25



Life Expectancy Diagram - MASTER TL-D Super 80 58W/830 1SL/25

# MASTER TL-D Super 80

## Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 58W/830 1SL/25

