



TL-D consumer products

TL-D 58W/840 1PP/10

The lamp can be operated in existing TL-D luminaire and is available in a wide range of wattages and colors.

Product data

| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life To 10% Failures (Nom) | 12000 h |
| Life to 50% Failures (Nom) | 15000 h |
| Life to 50% Failures Preheat (Nom) | 20000 h |
| LSF 2000 h Rated | 99 % |
| LSF 4000 h Rated | 99 % |
| LSF 6000 h Rated | 99 % |
| LSF 8000 h Rated | 99 % |
| LSF 12000 h Rated | 89 % |
| LSF 16000 h Rated | 33 % |
| LSF 20000 h Rated | 2 % |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux (Nom) | 5240 lm |
| Luminous Flux (Rated) (Nom) | 5240 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 90 lm/W |
| Color Rendering Index (Nom) | >80 |
| LLMF 2000 h Rated | 96 % |

| | |
|--------------------|------|
| LLMF 4000 h Rated | 95 % |
| LLMF 6000 h Rated | 94 % |
| LLMF 8000 h Rated | 93 % |
| LLMF 12000 h Rated | 92 % |
| LLMF 16000 h Rated | 91 % |
| LLMF 20000 h Rated | 90 % |

Operating and Electrical

| | |
|--------------------|---------|
| Power (Nom) | 58.5 W |
| Lamp Current (Nom) | 0.670 A |

Temperature

| | |
|--------------------------|-------|
| Design Temperature (Nom) | 25 °C |
|--------------------------|-------|

Controls and Dimming

| | |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

Approval and Application

| | |
|-------------------------------|--------|
| Energy Efficiency Label (EEL) | A |
| Mercury (Hg) Content (Nom) | 2.0 mg |
| Energy Consumption kWh/1000 h | 68 kWh |

TL-D consumer products


Product Data

| | |
|-------------------------------|---------------------|
| Full product code | 871150062271625 |
| Order product name | TL-D 58W/840 1PP/10 |
| EAN/UPC - Product | 8711500622716 |
| Order code | 927922084022 |
| Numerator - Quantity Per Pack | 1 |

| | |
|---------------------------------|-------------------|
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 927922084022 |
| Net Weight (Piece) | 167.000 g |
| ILCOS Code | FD-58/40/1B-E-G13 |

Warnings and Safety


Dimensional drawing




| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---------------------|---------|-----------|-----------|-----------|-----------|
| TL-D 58W/840 1PP/10 | 28 mm | 1500.0 mm | 1507.1 mm | 1504.7 mm | 1514.2 mm |

TL-D 58W/840

Photometric data




LDPB_TL-D8_840_0001-Spectral power distribution B/W



LDPO_TL-D8_840_0001-Spectral power distribution Colour

TL-D consumer products

Lifetime



LDLE_TL-D8_0001-Life expectancy diagram

