

MASTER TL5 High Efficiency

MASTER TL5 HE 14W/865 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Product data

General Information	
Cap base	G5 [G5]
Life to 50% failures preheat (nom.)	24000 h
Features	na [Not Applicable]
System description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %

Light Technical	
Colour code	865 [CCT of 6,500 K]
Luminous flux (nom.)	1250 lm
Luminous flux (rated) (nom.)	1125 lm
Colour designation	Cool Daylight
Luminous efficacy (@ max. lumen, rated) (nom.)	91 lm/W
Correlated colour temperature (nom.)	6500 K
Luminous efficacy (rated) (nom.)	89 lm/W
Color rendering index (max.)	85
Color rendering index (min.)	80
Color rendering index (nom.)	82

LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	14 W
Lamp current (nom.)	0.165 A

Temperature	
Design temperature (nom.)	35 °C

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	Green Plate

Approval and Application	
Energy efficiency label (EEL)	A+

MASTER TL5 High Efficiency

Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Full product code	871150071009355
Order product name	MASTER TL5 HE 14W/865 SLV/40
EAN/UPC – product	8711500710093
Order code	71009355

Local Code	14865
Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927926086555
Net weight (piece)	52.000 g
ILCOS Code	FDH-14/65/1B-L/P-G5-16/550

Warnings and Safety


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 14W/865 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

TL5 14W/865/GP HE

Photometric data




Lightcolour /865



Lightcolour /865

MASTER TL5 High Efficiency

Lifetime



LDLE_TL5-HE8_0002-Life expectancy diagram

