

MASTER TL5 High Efficiency

MASTER TL5 HE 21W/865 UNP/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Product data

General Information	
Cap base	G5 [G5]
Life to 50% failures preheat (nom.)	24000 h
Features	na [Not Applicable]
System description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %

Light Technical	
Colour code	865 [CCT of 6,500 K]
Luminous flux (nom.)	1950 lm
Luminous flux (rated) (nom.)	1725 lm
Colour designation	Cool Daylight
Luminous efficacy (@ max. lumen, rated) (nom.)	94 lm/W
Correlated colour temperature (nom.)	6500 K
Luminous efficacy (rated) (nom.)	84 lm/W
Color rendering index (max.)	85
Color rendering index (min.)	80
Color rendering index (nom.)	82

LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	20.6 W
Lamp current (nom.)	0.165 A

Temperature	
Design temperature (nom.)	35 °C

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	Green Plate

Approval and Application	
Energy efficiency label (EEL)	A+

MASTER TL5 High Efficiency


Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	23 kWh
Product Data	
Full product code	87115006107755
Order product name	MASTER TL5 HE 21W/865 UNP/40
EAN/UPC – product	8711500610775
Order code	61077555

Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927926286518
Net weight (piece)	80.500 g
ILCOS Code	FDH-21/65/1B-L/P-G5-16/850

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




TL5 21W/865/GP HE

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 21W/865 UNP/40	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

Photometric data



Lightcolour /865



Lightcolour /865

MASTER TL5 High Efficiency

Lifetime

