



# MASTER TL5 High Output

## MASTER TL5 HO 49W/830 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Product data

General Information	
Cap base	G5 [ G5]
Life to 50% failures preheat (nom.)	30000 h
Features	na [ Not Applicable]
System description	High Output (HO)
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %

Light Technical	
Colour code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	4900 lm
Luminous flux (rated) (nom.)	4375 lm
Colour designation	Warm white (WW)
Luminous efficacy (@ max. lumen, rated) (nom.)	99 lm/W
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	89 lm/W
Color rendering index (max.)	85
Color rendering index (min.)	80
Color rendering index (nom.)	82

LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	49.2 W
Lamp current (nom.)	0.255 A

Temperature	
Design temperature (nom.)	35 °C

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	Green Plate

Approval and Application	
Energy efficiency label (EEL)	A+


# MASTER TL5 High Output

Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	54 kWh
<b>Product Data</b>	
Full product code	871150063954755
Order product name	MASTER TL5 HO 49W/830 SLV/40
EAN/UPC – product	8711500639547
Order code	63954755

Local Code	49830
Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927927583055
Net weight (piece)	128.700 g
ILCOS Code	FDH-49/30/1B-L/P-G5-16/1450

## Warnings and Safety



## Dimensional drawing



**Product**  
MASTER TL5 HO 49W/830 SLV/40

**TL5 HO 49W/830**

## Photometric data




**Lightcolour /830**


**Lightcolour /830**

# MASTER TL5 High Output

## Lifetime



LDLE\_TL5-HO8\_0002-Life expectancy diagram



LDLM\_TL5-HO8\_0001-Lumen maintenance diagram

