



PL-Q 4 Pin

PL-Q 28W/827/4P 1CT/10BOX

Compact fluorescent lamps with a quadrant-like shape

Product data

General Information	
Cap base	GR10Q [GR10q]
Life to 50% failures preheat (nom.)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	95 %
LSF Preheat 8000 h Rated	89 %
LSF Preheat 16000 h Rated	22 %
LSF Preheat 20000 h Rated	4 %

Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	2050 lm
Lamp Luminous Flux (Nom)	2050 lm
Colour Designation	Incandescent White
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	73.2 lm/W
Colour Rendering Index, horiz (Nom)	82
LLMF 2000 h Rated	90 %
LLMF 4000 h Rated	86 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	80 %
LLMF 12000 h Rated	79 %
LLMF 16000 h Rated	78 %
LLMF 20000 h Rated	78 %

Operating and Electrical	
Power (Rated) (Nom)	24.8 W
Lamp current (nom.)	0.320 A

Temperature	
Design temperature (nom.)	25 °C

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	4P

Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4 mg
Energy Consumption kWh/1000 h	31 kWh


Product Data	
Full product code	871150026991125
Order product name	PL-Q 28W/827/4P 1CT/10BOX
EAN/UPC – product	8711500269911
Order code	927939382740
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (I2NC)	927939382740

PL-Q 4 Pin

Net weight (piece)	127.000 g
ILCOS Code	FSS-28/27/1B-E-GR10q

Warnings and Safety



Dimensional drawing



Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 28W/ 827/4P 1CT/ 10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm

PL-Q 28W/827/4P


Photometric data



Lightcolour /827

Lightcolour /827

Lifetime




LDLM_PLQ4P_0001-Lumen maintenance diagram

LDLE_PLQ4P_0002-Life expectancy diagram

PL-Q 4 Pin

Lifetime



LDLE_PLQ4P_0001-Life expectancy diagram

