



# T8 900 Series Rapid Start

## F32T8/TL950 98CRI 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.


### Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T-8
Life to 50% Failures (Nom)	15,000 hour(s)	Approval and Application	
Light Technical		Mercury (Hg) Content (Nom)	5.0 mg
Color Code	TL950 [CCT of 5000K (950)]	Product Data	
Luminous Flux	2,000 lm	Order product name	F32T8/TL950 SLV
Color Designation	TL950	Full product name	F32T8/TL950 98CRI 25PK
Correlated Color Temperature (Nom)	5000 K	Order code	209056
Luminous Efficacy (rated) (Nom)	63.9 lm/W	Material Nr. (12NC)	927942009520
Color rendering index (CRI)	98	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	046677209056
Power Consumption	32 W	Numerator - Packs per outer box	25
Lamp Current (Nom)	0.265 A	EAN/UPC - Case	50046677209051
Wattage Equivalent	32 W		
Voltage (Nom)	139 V		
Voltage (Nom)	139 V		
Controls and Dimming			
Dimmable	Yes		


# T8 900 Series Rapid Start

## Dimensional drawing

Product
F32T8/TL950 SLV



## Photometric data



Spectral Power Distribution Colour - F32T8/TL950 SLV

