



TUV T5

TUV 64T5 HO 4P SE UNP/32

TUV T5 lamps are single- or double-ended UVC (germicidal) lamps used in professional water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data

General Information	
Cap-Base	4PINSSINGLEENDED [4 Pins Single Ended]
Useful Life (Nom)	9,000 h
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	20 %
Operating and Electrical	
Power Consumption	140 W
Lamp Current (Nom)	0.8 A
Voltage (Nom)	175 V


Voltage (Nom)	175 V
Mechanical and Housing	
Bulb Shape	T16
Approval and Application	
Mercury (Hg) Content (Nom)	5.5 mg
UV	
UV-C Radiation at 100 hr	50.6 W
Product Data	
Order product name	TUV 64T5 HO 4P SE UNP/32
Full product name	TUV 64T5 HO 4P SE UNP/32

TUV T5

Full product code	871150026131199
Local code description	TUV64WT5HO4PSE
Order code	927971104099
Material Nr. (12NC)	927971104099
Local order code	TUV64WT5HO4PSE
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500261311
Numerator - Packs per outer box	32
EAN/UPC - Case	8711500261328

Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 64T5 HO 4P SE UNP/32	19.3 mm	1,564.5 mm	1,555.2 mm

Photometric data



Spectral Power Distribution Colour - TUV 64T5 HO 4P SE UNP/32

