



UV-B Narrowband TL

TL F72T12 100W/01 UV-B

More than 400 independent clinical studies have proven that the UVB Narrowband TL lamps are safer and more effective than any other lamps in their class. That is because these lamps emit only a very narrow waveband from the 'B' bandwidth of the UV spectrum (290 to 315). This narrow waveband is between 305 and 315 nm and peaks at 311 nm: the most efficacious waveband for the treatment of psoriasis. This means that treatment is much more focused and exposure times are much shorter. This in turn leads to a reduction of side effects such as reddening of the skin and itching. All of this makes them ideal for phototherapy treatment of diseases such as psoriasis and vitiligo. What's more, because the overall dosage of this narrowband radiation can be closely controlled, these lamps are suitable for home therapy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Chromaticity Coordinate Y (Nom)	
Cap-Base	RDC [RDC]	UV Depreciation at 1000 h	208
Life to 50% Failures (Nom)	1,000 hour(s)	UV Depreciation at 500 h	15 %
Useful Life (Nom)	1,000 hour(s)		10 %
Light Technical		Operating and Electrical	
Color Code	01	Power Consumption	100 W
Color Designation	Ultra Violet B	Lamp Current (Nom)	0.97 A
Chromaticity Coordinate X (Nom)	216	Voltage (Nom)	126 V

UV-B Narrowband TL

Voltage (Nom)	126 V
Mechanical and Housing	
Bulb Shape	T38 [T 38mm]
Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
UV	
UV-B Radiation 100 hr (IEC)	15 W
Product Data	
Order product name	TL F72T12 100W/01 UV-B


Full product name	TL F72T12 100W/01 UV-B
Full product code	871869666235900
Order code	323196
Material Nr. (12NC)	927978500130
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696662359
Numerator - Packs per outer box	25
EAN/UPC - Case	8718696662366

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL F72T12 100W/01 UV-B	1-5/8 inch	69-1/8 inch	69-7/16 inch	69-5/16 inch	69-15/16 inch

Photometric data



Spectral Power Distribution Colour - TL F72T12 100W/01 UV-B

UV-B Narrowband TL

