



TL-D LIFEMAX Super 80

TL-D 18W/830 1SL/25


The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

Informasi Umum		Mekanis dan Housing	
Tutup-Dasar	G13 [Medium Bi-Pin Fluorescent]	Bentuk Bohlam	T8 [26 mm (T8)]
Nominal masa pakai	15.000 jam		
Masa Pakai hingga 50 % Kegagalan (Nom)	13.000 jam		
Teknis Lampu		Penyetujuan dan Aplikasi	
Kode Warna	830 [CCT of 3000K]	Kandungan Merkuri (Hg) (Nom)	2,0 mg
Penandaan Warna	Warm White (WW)		
Suhu Warna Terkorelasi (Nom)	3000 K		
Daya Penerangan (terukur) (Nom)	75 lm/W		
Indeks renderasi warna (CRI)	83		
Pengoperasian dan Kelistrikan		Data Produk	
Konsumsi Daya	18 W	Nama produk pesanan	TL-D 18W/830 1SL/25
Arus Lampu (Nom)	0,360 A	Nama lengkap produk	TL-D 18W/830 1SL/25
Tegangan (Nom)	59 V	Kode produk lengkap	871150028558400
Tegangan (Nom)	59 V	Kode urutan	927980283036
		No. Material (12NC)	927980283036
		Numerator - Jumlah Per Pak	1
		EAN/UPC - Produk/Kantung	8711500285584
		Numerator - Pak per kotak bagian luar	25
		EAN/UPC - Kantung	8711500285799
Kontrol dan Peredupan			
Dapat diredupkan	Ya		


TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/830 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Photometric data




Spectral Power Distribution Colour - TL-D 18W/830 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 18W/830 1SL/25



Life Expectancy Diagram - TL-D 18W/830 1SL/25

TL-D LIFEMAX Super 80

Lifetime



Lumen Maintenance Diagram - TL-D 18W/830 1SL/25

