



# MASTER TL-D Super 80

## TL-D 36W/830 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h

Light Technical	
Colour Code	830 [ CCT of 3,000 K]
Lamp Luminous Flux (Nom)	3250 lm
Colour Designation	Warm white (WW)
Lumen maintenance 2,000 hours (nom.)	96 %
Lumen maintenance 5,000 hours (nom.)	94 %
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Nom)	90 lm/W
Colour Rendering Index,horiz (Nom)	83

Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp current (nom.)	0.440 A
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	Green [ Green Cap]

Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg


  

Product Data	
Full product code	871829125420100
Order product name	TL-D 36W/830 1SL/25
EAN/UPC – product	8718291254201
Order code	927981383024
Local Code	TLD36W830ALTO
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927981383024
Net weight (piece)	0.140 kg

# MASTER TL-D Super 80

## Warnings and Safety


## Dimensional drawing



TL-D 36W/830

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/830 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm


## Photometric data




LDPB\_TL-D8G\_830-Spectral power distribution B/W

LDPO\_TL-D8G\_830-Spectral power distribution Colour

## Lifetime




LDLE\_TL-D8G\_0001-Life expectancy diagram



LDLE\_TL-D8G\_0002-Life expectancy diagram

# MASTER TL-D Super 80

## Lifetime



LDLM\_TL-D8G\_0001-Lumen maintenance diagram

