

# TL-D LIFEMAX Super 80

## TL-D 36W/830 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.


### Product data

Informasi Umum	
Tutup-Dasar	G13 [Medium Bi-Pin Fluorescent]
Nominal masa pakai	15.000 jam
Masa Pakai hingga 50 % Kegagalan (Nom)	15.000 jam
Teknis Lampu	
Kode Warna	830 [CCT of 3000K]
Penandaan Warna	Warm White (WW)
Suhu Warna Terkorelasi (Nom)	3000 K
Daya Penerangan (terukur) (Nom)	90 lm/W
Indeks renderasi warna (CRI)	83
Pengoperasian dan Kelistrikan	
Konsumsi Daya	36 W
Arus Lampu (Nom)	0,440 A
Tegangan (Nom)	103 V
Tegangan (Nom)	103 V
Kontrol dan Peredupan	
Dapat direduksi	Ya

Mekanis dan Housing	
Bentuk Bohlam	T8
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	2,0 mg
Data Produk	
Nama produk pesanan	TL-D 36W/830 1SL/25
Nama lengkap produk	TL-D 36W/830 1SL/25
Kode produk lengkap	871150028559140
Kode urutan	927982283036
No. Material (12NC)	927982283036
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500285591
Numerator - Pak per kotak bagian luar	25
EAN/UPC - Kantung	8711500285874


# TL-D LIFEMAX Super 80

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/830 1SL/25	28 mm	1.199,4 mm	1.206,5 mm	1.204,1 mm	1.213,6 mm

## Photometric data




Spectral Power Distribution Colour - TL-D 36W/830 1SL/25

## Lifetime




Life Expectancy Diagram - TL-D 36W/830 1SL/25



Life Expectancy Diagram - TL-D 36W/830 1SL/25

## TL-D LIFEMAX Super 80

### Lifetime



Lumen Maintenance Diagram - TL-D 36W/830 1SL/25

