



TL-D LIFEMAX Super 80

TL-D 58W/840 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h

Light Technical	
Color Code	841 [CCT of 4100K (841)]
Luminous Flux (Rated) (Nom)	5150 lm
Color Designation	Cool White (CW)
Lumen Maintenance 2000 h (Nom)	96 %
Lumen Maintenance 5000 h (Nom)	94 %
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color Rendering Index (Nom)	82

Operating and Electrical	
Power (Rated) (Nom)	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Cap-Base Information	Green [Green Base]

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg

Product Data	
Full product code	871150028492140
Order product name	TL-D 58W/840 1SL/25
EAN/UPC - Product	8711500284921
Order code	927983284036
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927983284036
Net Weight (Piece)	0.230 kg

TL-D LIFEMAX Super 80

Dimensional drawing




TL-D 58W/840/GC


Product

TL-D 58W/840 1SL/25


Lifetime



TL-D Super 80 Life Expectancy 3 h cycle



TL-D Super 80 Life Expectancy 12 h cycle



TL-D Super 80 Lumen Maintenance 3 h + 12 h cycle

TL-D LIFEMAX Super 80

