

TL-D LIFEMAX Super 80

TL-D 58W/840 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V
Voltage (Nom)	111 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	TL-D 58W/840 1SL/25
Full product name	TL-D 58W/840 1SL/25
Full product code	871150028492140
Order code	927983284036
Material Nr. (12NC)	927983284036
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500284921
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500284938



TL-D LIFEMAX Super 80

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/840 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Lifetime



Life Expectancy Diagram - TL-D 58W/840 1SL/25

Life Expectancy Diagram - TL-D 58W/840 1SL/25



Lumen Maintenance Diagram - TL-D 58W/840 1SL/25

TL-D LIFEMAX Super 80

