



# MASTER TL5 High Output Eco

## MASTER TL5 HO Eco 20=24W/840 UNP/40

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HO Eco lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

### Product data

General Information	
Cap-Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	na [ Not Applicable]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	99 %
LSF Preheat 20000 h Rated	94 %
Light Technical	
Color Code	841 [ CCT of 4100K (841)]
Luminous Flux (Nom)	1950 lm
Luminous Flux (Rated) (Nom)	1650 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	99 lm/W
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	85 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	19.5 W
Lamp Current (Nom)	0.300 A
Temperature	
Design Temperature (Nom)	35 °C

# MASTER TL5 High Output Eco

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application

Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	22 kWh


## Product Data

Full product code	872790088086100
Order product name	MASTER TL5 HO Eco 20=24W/840 UNP/40

EAN/UPC - Product	8711500881311
Order code	927989984031
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927989984031
Net Weight (Piece)	52.000 g
ILCOS Code	FDH-20/40/1B-L/P-G5-16/550

## Warnings and Safety



## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Eco 20=24W/840 UNP/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

## TL5 HO Eco 20=24W/840

## Photometric data




## Lightcolor /840

## Lightcolor /840


# MASTER TL5 High Output Eco

## Lifetime



MASTER TL5 HO Eco Life Expectancy 3 h cycle

MASTER TL5 HO Eco Life Expectancy 12 h cycle



MASTER TL5 HO Eco Lumen Maintenance 3 h + 12 h cycle

