



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL MINI 4W/10 /10X25CC

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Product data


General Information	
Cap base	G5 [G5]
Life to 50% failures (nom.)	8000 h
Useful life (max.)	5000 h
Light Technical	
Colour code	10
Colour designation	Actinic
Depreciation at 1000 Hours	25 %
Depreciation at 500 Hours	35 %
Depreciation at 500 Hours	17 %
Operating and Electrical	
Power (Rated) (Nom)	4.5 W
Lamp current (nom.)	0.17 A
Voltage (Nom)	29 V

Approval and Application	
Mercury (Hg) content (nom.)	4.4 mg
UV	
UV-B/UV-A (IEC)	0.2 %
Product Data	
Full product code	871150095142727
Order product name	Actinic BL TL MINI 4W/10
EAN/UPC – product	8711500951427
Order code	95142727
Numerator – quantity per pack	1
Numerator – packs per outer box	250
Material no. (12NC)	928000001030
Net weight (piece)	18.600 g

Actinic BL TL(-K)/TL-D(-K)

Warnings and Safety


Dimensional drawing




TL 4W/10

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 4W/10	16 mm	135.9 mm	143 mm	140.6 mm	150.1 mm

Photometric data



XDPB_XUBTL_10-Spectral power distribution B/W



XDPO_XUBTL_10-Spectral power distribution Colour

