



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL 6W/10 1FM/10X25CC

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Product data


General Information		Operating and Electrical	
Cap base	G5 [G5]	Power (Rated) (Nom)	6 W
Main application	Insect traps	Lamp current (nom.)	0.16 A
Life to 50% failures (nom.)	10000 h	Voltage (Nom)	42 V
Useful life (nom.)	5000 h		
Light Technical		Approval and Application	
Colour code	10	Mercury (Hg) content (nom.)	4.4 mg
Colour designation	Actinic		
Chromaticity coordinate X (nom.)	222	UV	
Chromaticity coordinate Y (nom.)	210	UV-B/UV-A (IEC)	0.2 %
Depreciation at 500 Hours	17 %	UV-A radiation 100 hours (IEC)	1.4 W
Depreciation at 1000 Hours	25 %		
Depreciation at 500 Hours	35 %	Product Data	
Depreciation at 500 Hours	50 %	Full product code	871150026039027
Depreciation at 500 Hours	60 %	Order product name	Actinic BL TL 6W/10 1FM/10X25CC
		EAN/UPC – product	8711500260390
		Order code	26039027
		Numerator – quantity per pack	1

Actinic BL TL(-K)/TL-D(-K)

Numerator – packs per outer box	250
Material no. (12NC)	928000501030
Net weight (piece)	21.000 g

Warnings and Safety

Dimensional drawing



Product

Actinic BL TL 6W/10 1FM/10X25CC

TL 6W/10

Photometric data

