



# Actinic BL TL(-K)/TL-D(-K)

## Actinic BL TL 6W/10 1FM/10X25CC

Tubular low-pressure mercury vapour fluorescent lamps

### Product data

General Information	
Cap base	G5 [ G5]
Main application	Insect traps
Life to 50% failures (nom.)	10000 h
Useful life (nom.)	5000 h

Light Technical	
Colour Code	10
Colour Designation	Actinic
Chromaticity coordinate X (nom.)	222
Chromaticity coordinate Y (nom.)	210
Depreciation at 500 Hours	17 %
Depreciation at 1000 Hours	25 %
Depreciation at 500 Hours	35 %
Depreciation at 500 Hours	50 %
Depreciation at 500 Hours	60 %

Operating and Electrical	
Power (Rated) (Nom)	6 W
Lamp current (nom.)	0.16 A

Voltage (Nom)	42 V
---------------	------

Approval and Application	
Mercury (Hg) content (nom.)	4.4 mg


UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	1.4 W

Product Data	
Full product code	871150026039027
Order product name	Actinic BL TL 6W/10 1FM/10X25CC
EAN/UPC – product	8711500260390
Order code	928000501030
Numerator – quantity per pack	1
Numerator – packs per outer box	250
Material no. (12NC)	928000501030
Net weight (piece)	21.000 g

### Warnings and Safety

# Actinic BL TL(-K)/TL-D(-K)

## Dimensional drawing




### Product

Actinic BL TL 6W/10 1FM/10X25CC

TL 6W/10

## Photometric data



Lightcolour /10

Lightcolour /10

