



# Actinic BL TL(-K)/TL-D(-K)

## Actinic BL TL 6W/10 1FM/10X25CC

Tubular low-pressure mercury vapour fluorescent lamps

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Voltage (nom.)	
Cap base	G5 [G5]		42 V
Life to 50% failures (nom.)	10,000 h		42 V
Useful life (nom.)	5,000 h		
Light Technical		Mechanical and Housing	
Colour Code	10	Bulb shape	T16 [T 16 mm]
Colour designation	Actinic	Approval and Application	
Chromaticity Coordinate X (Nom)	222	Mercury (Hg) content (nom.)	4.4 mg
Chromaticity Coordinate Y (Nom)	210	UV	
UV depreciation at 1,000 h	25 %	UV-A radiation 100 hours (IEC)	1.4 W
UV depreciation at 2,000 h	35 %	Product Data	
UV Depreciation at 5,000 h	50 %	Order product name	Actinic BL TL 6W/10 1FM/10X25CC
UV depreciation at 500 hours	17 %	Full product name	Actinic BL TL 6W/10 1FM/10X25CC
UV depreciation at 8000 hours	60 %	Full EOC	871150026039027
Operating and Electrical		Order code	26039027
Power Consumption	6 W	Material no. (12 NC)	928000501030
Lamp current (nom.)	0.16 A	Local order code	610


# Actinic BL TL(-K)/TL-D(-K)

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500260390
Numerator – packs per outer box	250


EAN/UPC - Case	8711500260413
----------------	---------------

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 6W/10 1FM/10X25CC	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm



## Photometric data



Spectral Power Distribution Colour - Actinic BL TL 6W/10 1FM/10X25CC

