



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL 11W/10

Tubular low-pressure mercury vapour fluorescent lamps

Product data

General Information	
Cap base	G5 [G5]
Main application	Insect traps
Useful life (nom.)	2000 h

Light Technical	
Colour Code	10
Colour Designation	Actinic
Chromaticity coordinate X (nom.)	230
Chromaticity coordinate Y (nom.)	230
Depreciation at 500 Hours	30 %
Depreciation at 1000 Hours	40 %
Depreciation at 500 Hours	45 %

Operating and Electrical	
Power (Rated) (Nom)	11.5 W
Lamp current (nom.)	0.400 A
Voltage (Nom)	34 V

Approval and Application	
Mercury (Hg) content (nom.)	4.4 mg


UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	2.0 W

Product Data	
Full product code	871150095145827
Order product name	Actinic BL TL 11W/10
EAN/UPC – product	8711500951458
Order code	928000601030
Local Code	TL11W10
Numerator – quantity per pack	1
Numerator – packs per outer box	250
Material no. (12NC)	928000601030
Net weight (piece)	21.000 g

Warnings and Safety

Actinic BL TL(-K)/TL-D(-K)

Dimensional drawing




Product

Actinic BL TL 11W/10

TL 11W/10

Photometric data



Lightcolour /10

Lightcolour /10

