

# PHILIPS

## Lighting



# Actinic BL TL(-K)/TL-D(-K)

## Actinic BL TL 8W/10 1FM/10X25CC

Tubular low-pressure mercury vapour fluorescent lamps

### Product data

#### General Information

Cap base	G5 [ G5]
Main application	Reprography (R)
Life to 50% failures (nom.)	10000 h
Useful life (nom.)	5000 h

#### Light Technical

Colour code	10
Colour designation	Actinic
Chromaticity coordinate X (nom.)	222
Chromaticity coordinate Y (nom.)	210
Depreciation at 500 Hours	17 %
Depreciation at 1000 Hours	25 %
Depreciation at 5000 Hours	35 %

#### Operating and Electrical

Power (Rated) (Nom)	7.1 W
Lamp current (nom.)	0.145 A
Voltage (Nom)	56 V

#### Approval and Application

Mercury (Hg) content (nom.)	4.4 mg
-----------------------------	--------

#### UV

UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	1.60 W

#### Product Data


Full product code	871150026042027
Order product name	Actinic BL TL 8W/10 1FM/10X25CC
EAN/UPC – product	8711500260420
Order code	26042027
Local Code	810
Numerator – quantity per pack	1
Numerator – packs per outer box	250
Material no. (12NC)	928001001030
Net weight (piece)	25.300 g

# Actinic BL TL(-K)/TL-D(-K)

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 8W/10 1FM/ 10X25CC	16 mm	288.3 mm	295.4 mm	293 mm	302.5 mm

TL 8W/10

## Photometric data



Lightcolour /10



Lightcolour /10

