



TL Mini consumer products

TL Mini 8W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

Product data

General Information	
Cap base	G5 [G5]
Life to 10% failures (nom.)	5000 h
Life to 50% failures (nom.)	10000 h
Life to 50% failures preheat (nom.)	10000 h
System description	na [-]

Light Technical

Colour Code	33-640
Lamp Luminous Flux 25°C EL (Nom)	410 lm
Colour Designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	58 %
Lumen maintenance 2,000 hours (nom.)	80 %
Lumen maintenance 5,000 hours (nom.)	70 %
Colour Temperature, horizontal (Nom)	4100 K
Lamp Luminous Efficacy EM (Nom)	51 lm/W
Colour Rendering Index,horiz (Nom)	60

Operating and Electrical

Power (Rated) (Nom)	7.1 W
Lamp current (nom.)	0.145 A
Voltage (Nom)	56 V

Controls and Dimming	
Dimmable	yes


Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4.4 mg
Energy Consumption kWh/1000 h	8 kWh

Product Data

Full product code	871150062695025
Order product name	TL Mini 8W/33-640 1PP/10
EAN/UPC – product	8711500626950
Order code	928001003313
Local Code	TL8W33PP
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	928001003313
Net weight (piece)	27.000 g
ILCOS Code	FD-8/41/2B-E-G5

TL Mini consumer products


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/33-640	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm
1PP/10					

TL Mini 8W/33-640

Photometric data



Lightcolour /33-640



Lightcolour /33-640

