



# TL Mini consumer products



## TL MINI 8W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G5 [G5]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	10,000 h
Light Technical	
Colour Code	33-640
Luminous Flux	380 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	51 lm/W
Colour rendering index (CRI)	59
Operating and Electrical	
Power Consumption	7.1 W
Lamp current (nom.)	0.145 A

Voltage (nom.)	56 V
Voltage (nom.)	56 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	2.5 mg
Mercury (Hg) content (nom.)	4.4 mg
Energy consumption kWh/1,000 hours	8 kWh
EPREL registration number	423490
Product Data	
Order product name	TL Mini 8W/33-640 1PP/10


TL Mini consumer products

Full product name	TL MINI 8W/33-640 1PP/10
Full EOC	871150062695025
Order code	62695025
Material no. (12 NC)	928001003313
SAP numerator – quantity per pack	1


EAN/UPC – Product/Case	8711500626950
Numerator – packs per outer box	10
EAN/UPC – Case	8711500262080

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/33-640 1PP/10	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm



Photometric data



Spectral Power Distribution Colour – TL Mini 8W/33-640 1PP/10

