



TL Mini consumer products



TL MINI 13W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (nom.)	
Cap base	G5 [G5]		90 V
Flux measurement reference	Sphere		90 V
Life to 50% failures (nom.)	8,000 h		
Light Technical		Controls and Dimming	
Colour Code	33-640	Dimmable	Yes
Luminous Flux	835 lm	Mechanical and Housing	
Colour designation	Cool White (CW)	Bulb shape	T5 [16 mm (T5)]
Chromaticity Coordinate X (Nom)	0.38	Approval and Application	
Chromaticity Coordinate Y (Nom)	0.38	Energy Efficiency Class	G
Correlated Colour Temperature	4000 K	Mercury (Hg) content (max.)	2.5 mg
Luminous efficacy (rated) (nom.)	71 lm/W	Mercury (Hg) content (nom.)	4.4 mg
Colour rendering index (CRI)	59	Energy consumption kWh/1,000 hours	14 kWh
Operating and Electrical		EPREL registration number	423497
Power Consumption	13.1 W	Product Data	
Lamp current (nom.)	0.170 A	Order product name	TL Mini 13W/33-640 1PP/10

TL Mini consumer products

Full product name	TL MINI 13W/33-640 1PP/10
Full EOC	871150062698125
Order code	62698125
Material no. (12 NC)	928001503313
SAP numerator – quantity per pack	1


EAN/UPC – Product/Case	8711500626981
Numerator – packs per outer box	10
EAN/UPC – Case	8711500262110

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 13W/33-640 1PP/10	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

Photometric data



Spectral Power Distribution Colour – TL Mini 13W/33-640 1PP/10

