



TL Mini consumer products

TL Mini 13W/827 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

Product data

General Information	
Cap-Base	G5 [G5]
Life To 10% Failures (Nom)	4000 h
Life to 50% Failures (Nom)	8000 h
Life to 50% Failures Preheat (Nom)	8000 h

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	1000 lm
Color Designation	Incandescent White
Lumen Maintenance 10000 h (Nom)	71 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	77 %
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color Rendering Index (Nom)	82

Operating and Electrical	
Power (Nom)	13.0 W
Lamp Current (Nom)	0.170 A
Voltage (Nom)	90 V

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	14 kWh

Product Data	
Full product code	871150062257025
Order product name	TL Mini 13W/827 1PP/10
EAN/UPC - Product	8711500622570
Order code	928001508213
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	928001508213
Net Weight (Piece)	40.200 g
ILCOS Code	FD-13/27/1B-E-G5

TL Mini consumer products

Warnings and Safety

Dimensional drawing





Product

TL Mini 13W/827 1PP/10

TL 13W/827

Photometric data



LDPB_TL8MINI_827-Spectral power distribution B/W

