



UV-B Narrowband TL

TL 20W/01 RS SLV/25

More than 400 independent clinical studies have proven that the UVB Narrowband TL lamps are safer and more effective than any other lamps in their class. That is because these lamps emit only a very narrow waveband from the 'B' bandwidth of the UV spectrum (290 to 315). This narrow waveband is between 305 and 315 nm and peaks at 311 nm: the most efficacious waveband for the treatment of psoriasis. This means that treatment is much more focused and exposure times are much shorter. This in turn leads to a reduction of side effects such as reddening of the skin and itching. All of this makes them ideal for phototherapy treatment of diseases such as psoriasis and vitiligo. What's more, because the overall dosage of this narrowband radiation can be closely controlled, these lamps are suitable for home therapy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		UV Depreciation at 500 h	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		10 %
Life to 50% Failures (Nom)	2,000 hour(s)	Operating and Electrical	
Useful Life (Nom)	2,000 hour(s)	Power Consumption	19.3 W
Light Technical		Lamp Current (Nom)	0.37 A
Color Code	01	Voltage (Nom)	59 V
Color Designation	Ultra Violet B	Voltage (Nom)	59 V
Chromaticity Coordinate X (Nom)	208	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	192	Bulb Shape	T38
UV Depreciation at 1000 h	15 %		

UV-B Narrowband TL

Approval and Application

Mercury (Hg) Content (Nom) 5.5 mg

UV

UV-B Radiation 100 hr (IEC) 3.08 W

UV-B Radiation 5hr (IEC) 3.23 W

Product Data

Order product name TL 20W/01 RS SLV/25

Full product name TL 20W/01 RS SLV/25

Full product code 871869666237300

Order code 66237300

Material Nr. (12NC) 928010000130


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8718696662373

Numerator - Packs per outer box 25


EAN/UPC - Case 8718696662380

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 20W/01 RS SLV/25	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Spectral Power Distribution Colour - TL 20W/01 RS SLV/25

