



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL 40W/10 SLV/25

Tubular low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	9,000 hour(s)
Useful Life (Nom)	5,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	220
Chromaticity Coordinate Y (Nom)	205
UV Depreciation at 2000 h	20 %
UV Depreciation at 5000 h	40 %
Operating and Electrical	
Power Consumption	39 W
Lamp Current (Nom)	0.43 A
Voltage (Nom)	101 V
Voltage (Nom)	101 V

Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
UV	
UV-A Radiation 0Hr (IEC)	12.4 W
UV-A Radiation 100Hr (IEC)	10.0 W
Product Data	
Order product name	Actinic BL TL 40W/10 SLV/25
Full product name	Actinic BL TL 40W/10 SLV/25
Full product code	871150026026000
Order code	928011301020
Material Nr. (12NC)	928011301020
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260260
Numerator - Packs per outer box	25

Actinic BL TL(-K) / TL-D(-K)


EAN/UPC - Case	8711500260277
----------------	---------------

Dimensional drawing



Product	D (max)	A (max)	B	C (max)
Actinic BL TL 40W/10 SLV/25	37.25 mm	1,198.4 mm	1,205.4 mm	1,212.4 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL 40W/10 SLV/25

