



TL Rapid Start Standard Colours

TL RS 40W/54-765 1SL/25

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13000 h
System Description	Rapid Start
Light Technical	
Color Code	54-765
Luminous Flux (Nom)	2500 lm
Color Designation	Cool Daylight
Lumen Maintenance 10000 h (Nom)	73 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	81 %
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	64 lm/W
Color Rendering Index (Nom)	72
Operating and Electrical	
Power (Nom)	39.0 W
Lamp Current (Nom)	0.430 A
Voltage (Nom)	101 V

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Full product code	871150064133500
Order product name	TL RS 40W/54-765 1SL/25
EAN/UPC - Product	8711500641335
Order code	928011305430
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928011305430
Net Weight (Piece)	0.270 kg
ILCOS Code	FD-40/62/2A-L/P-G13

TL Rapid Start Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL RS 40W/54-765	40.5 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
1SL/25					

TL 40W/54-765 RS

Photometric data

