



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL-DK 30W/10

Tubular low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	2,000 h
Useful life (nom.)	2,000 h
Light Technical	
Colour Code	10
Colour designation	Actinic
Chromaticity Coordinate X (Nom)	225
Chromaticity Coordinate Y (Nom)	230
UV depreciation at 1,000 h	25 %
UV depreciation at 2,000 h	40 %
UV depreciation at 500 hours	15 %
Operating and Electrical	
Power Consumption	30 W
Lamp current (nom.)	0.805 A
Voltage (nom.)	45 V

Voltage (nom.)	45 V
Mechanical and Housing	
Bulb shape	T26 [T 26 mm]
Approval and Application	
Mercury (Hg) content (nom.)	8.0 mg
UV	
UV-A radiation 100 hours (IEC)	6.6 W
Product Data	
Order product name	ACTINIC BL TL-DK - 30W/10 1SL
Full product name	Actinic BL TL-DK 30W/10
Full EOC	871150089346840
Order code	89346840
Material no. (12 NC)	928019501029
Local order code	TLDK3010
SAP numerator – quantity per pack	1

Actinic BL TL(-K)/TL-D(-K)


EAN/UPC — Product/Case	8711500893468
Numerator – packs per outer box	25
EAN/UPC – Case	8711500893475

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
ACTINIC BL TL-DK - 30W/10 1SL	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data



Spectral Power Distribution Colour - ACTINIC BL TL-DK - 30W/10 1SL

