



# Actinic BL TL(-K)/TL-D(-K)

## ACTINIC BL30W/10 25PK

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.


### Product data

| General Information             |                                  | Voltage (Nom)                   |                               |
|---------------------------------|----------------------------------|---------------------------------|-------------------------------|
| Base                            | G13 [ Medium Bi-Pin Fluorescent] |                                 | 45 V                          |
| Main Application                | Insect traps                     | Approval and Application        |                               |
| Life to 50% Failures (Nom)      | 2000 h                           | Mercury (Hg) Content (Nom)      | 8.0 mg                        |
| Useful Life (Nom)               | 2000 h                           | UV                              |                               |
| Light Technical                 |                                  | UV-B/UV-A (IEC)                 | 02 %                          |
| Color Code                      | 10                               | UV-A Radiation 100Hr (IEC)      | 6.6 W                         |
| Color Designation               | Actinic                          | Product Data                    |                               |
| Chromaticity Coordinate X (Nom) | 225                              | XUCDM.COPY.Product.Title        | ACTINIC BL TL-DK - 30W/10 1SL |
| Chromaticity Coordinate Y (Nom) | 230                              | EAN/UPC - Product               | 8711500893468                 |
| UV Depreciation at 500 h        | 15 %                             | Order code                      | 215178                        |
| UV Depreciation at 1000 h       | 25 %                             | Numerator - Quantity Per Pack   | 1                             |
| UV Depreciation at 2000 h       | 40 %                             | Numerator - Packs per outer box | 25                            |
| Operating and Electrical        |                                  | Material Nr. (12NC)             | 928019501029                  |
| Power (Rated) (Nom)             | 30 W                             | Net Weight (Piece)              | 59.600 g                      |
| Lamp Current (Nom)              | 0.805 A                          |                                 |                               |

# Actinic BL TL(-K)/TL-D(-K)

## Warnings and Safety

## Dimensional drawing




### Product


ACTINIC BL TL-DK - 30W/10 1SL

TL-DK 30W/10

## Photometric data



XDPB\_XUATLDK\_10-Spectral power distribution B/W



XDPO\_XUATLDK\_10-Spectral power distribution Colour

