



Actinic BL TL(-K) / TL-D(-K)

ACTINIC BL30W/10 25PK

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


| General Information | | UV Depreciation at 1000 h | |
|---------------------------------|---------------------------------|---------------------------|---------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] | UV Depreciation at 2000 h | 25 % |
| Life to 50% Failures (Nom) | 2,000 hour(s) | UV Depreciation at 500 h | 40 % |
| Useful Life (Nom) | 2,000 hour(s) | | 15 % |
| Light Technical | | Operating and Electrical | |
| Color Code | 10 | Power Consumption | 30 W |
| Color Designation | Actinic | Lamp Current (Nom) | 0.805 A |
| Chromaticity Coordinate X (Nom) | 225 | Voltage (Nom) | 45 V |
| Chromaticity Coordinate Y (Nom) | 230 | Voltage (Nom) | 45 V |

Actinic BL TL(-K) / TL-D(-K)

| | |
|----------------------------|-------------------------------|
| Mechanical and Housing | |
| Bulb Shape | T26 [T 26mm] |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 8.0 mg |
| UV | |
| UV-A Radiation 100Hr (IEC) | 6.6 W |
| Product Data | |
| Order product name | ACTINIC BL TL-DK - 30W/10 1SL |


| | |
|---------------------------------|-----------------------|
| Full product name | ACTINIC BL30W/10 25PK |
| Full product code | 871150089346840 |
| Order code | 215178 |
| Material Nr. (12NC) | 928019501029 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500893468 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8711500893475 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|-------------------------------|------------|-------------|-------------|--------------|---------------|
| ACTINIC BL TL-DK - 30W/10 1SL | 1-1/8 inch | 17-1/4 inch | 17-1/2 inch | 17-7/16 inch | 17-13/16 inch |

Photometric data



Spectral Power Distribution Colour - ACTINIC BL TL-DK - 30W/10 1SL

Actinic BL TL(-K) / TL-D(-K)

