



# Actinic BL TL(-K)/TL-D(-K)

## Actinic BL TL-DK 36W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Product data


General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Main application	Reprography (R)
Life to 50% failures (nom.)	9000 h
Useful life (nom.)	5000 h
Light Technical	
Colour code	10
Colour designation	Actinic
Chromaticity coordinate X (nom.)	225
Chromaticity coordinate Y (nom.)	230
Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp current (nom.)	0.865 A
Voltage (Nom)	50 V

Approval and Application	
Mercury (Hg) content (nom.)	8.0 mg
UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	8.8 W
Product Data	
Full product code	872790086083200
Order product name	Actinic BL TL-DK 36W/10 1SL/25
EAN/UPC – product	8727900860832
Order code	86083200
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928019701003
Net weight (piece)	68.900 g

# Actinic BL TL(-K)/TL-D(-K)

## Warnings and Safety


## Dimensional drawing




TL-DK 36W/10

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-DK 36W/10 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

## Photometric data



XDPB\_XUATLDK\_10-Spectral power distribution B/W



XDPO\_XUATLDK\_10-Spectral power distribution Colour

