



# Actinic BL TL-D(K) Secura

## Actinic BL TL-D TL-D 15W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

### Product data

General Information		Voltage (Nom)	
Cap base	G13 [ Medium Bi-Pin Fluorescent]		51 V
Main application	Insect traps	Approval and Application	
Life to 50% failures (nom.)	11000 h	Mercury (Hg) content (nom.)	5.5 mg
Useful life (nom.)	9000 h	UV	
Light Technical		UV-B/UV-A (IEC)	0.2 %
Colour Code	10	UV-A radiation 100 hours (IEC)	3.15 W
Colour Designation	Actinic	Product Data	
Chromaticity coordinate X (nom.)	222	Full product code	871150089858640
Chromaticity coordinate Y (nom.)	210	Order product name	Actinic BL TL-D TL-D 15W/10 Secura 1SL/25
Depreciation at 500 Hours	25 %	EAN/UPC – product	8711500898586
Depreciation at 500 Hours	40 %	Order code	928024701029
Operating and Electrical		Numerator – quantity per pack	1
Power (Rated) (Nom)	15 W	Numerator – packs per outer box	25
Lamp current (nom.)	0.335 A	Material no. (12NC)	928024701029

# Actinic BL TL-D(K) Secura

Net weight (piece)	61.000 g
--------------------	----------



## Warnings and Safety

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D TL-D 15W/10 Secura 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

### TL-D 15W/10 SECU

## Photometric data



### Lightcolour /10

### Lightcolour /10

