



# Actinic BL TL-D(K) Secura

## ACTINIC BL15W/10 SECURA 25PK

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		Chromaticity Coordinate Y (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	210	
Life to 50% Failures (Nom)	8,000 hour(s)	UV Depreciation at 2000 h	
Useful Life (Nom)	9,000 hour(s)	25 %	
		UV Depreciation at 5000 h	
		40 %	
Light Technical		Operating and Electrical	
Color Code	10	Power Consumption	15 W
Color Designation	Actinic	Lamp Current (Nom)	0.335 A
Chromaticity Coordinate X (Nom)	222	Voltage (Nom)	55 V

Actinic BL TL-D(K) Secura

Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	5
UV	
UV-A Radiation 100Hr (IEC)	3.15 W
Product Data	
Order product name	Actinic BL TL-D 15W/10 Secura 1SL/25


Full product name	ACTINIC BL15W/10 SECURA 25PK
Full product code	871150089858640
Order code	215186
Material Nr. (12NC)	928024701029
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500898586
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500898593

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	1-1/8 inch	17-1/4 inch	17-1/2 inch	17-7/16 inch	17-13/16 inch

Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 15W/10 Secura 1SL/25

## Actinic BL TL-D(K) Secura

