



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL-D 15W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.


Product data

General Information		Voltage (Nom)	
Cap base	G13 [Medium Bi-Pin Fluorescent]		51 V
Main application	Reprography (R)	Approval and Application	
Life to 50% failures (nom.)	8000 h	Mercury (Hg) content (nom.)	5.0 mg
Useful life (nom.)	5000 h	UV	
Light Technical		UV-B/UV-A (IEC)	0.2 %
Colour code	10	UV-A radiation 100 hours (IEC)	3.5 W
Colour designation	Actinic	Product Data	
Chromaticity coordinate X (nom.)	222	Full product code	871150071093240
Chromaticity coordinate Y (nom.)	210	Order product name	Actinic BL TL-D 15W/10 1SL/25
Depreciation at 500 Hours	10 %	EAN/UPC – product	8711500710932
Depreciation at 500 Hours	15 %	Order code	71093240
Depreciation at 500 Hours	20 %	Numerator – quantity per pack	1
Operating and Electrical		Numerator – packs per outer box	25
Power (Rated) (Nom)	15 W	Material no. (12NC)	928024801029
Lamp current (nom.)	0.34 A	Net weight (piece)	56.570 g

Actinic BL TL(-K)/TL-D(-K)

Warnings and Safety



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

TL-D 15W/10

Photometric data



XDPB_XUBTLD_10-Spectral power distribution B/W

