



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL-D 15W/10 1SL/25

Tubular low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	8,000 h
Useful life (nom.)	9,000 h

Light Technical	
Colour Code	10
Colour designation	Actinic
Chromaticity Coordinate X (Nom)	222
Chromaticity Coordinate Y (Nom)	210
UV depreciation at 2,000 h	10 %
UV Depreciation at 5,000 h	15 %
UV depreciation at 8000 hours	20 %

Operating and Electrical	
Power Consumption	15 W
Lamp current (nom.)	0.34 A
Voltage (nom.)	55 V

Voltage (nom.)	55 V
Mechanical and Housing	
Bulb shape	T26 [T 26 mm]

Approval and Application	
Mercury (Hg) content (nom.)	5.0 mg

UV	
UV-A radiation 100 hours (IEC)	3.9 W


Product Data	
Order product name	Actinic BL TL-D 15W/10 1SL/25
Full product name	Actinic BL TL-D 15W/10 1SL/25
Full EOC	871150071093240
Order code	71093240
Material no. (12 NC)	928024801029
Local order code	TLD1510
SAP numerator – quantity per pack	1

Actinic BL TL(-K)/TL-D(-K)


EAN/UPC – Product/Case	8711500710932
Numerator – packs per outer box	25
EAN/UPC - Case	8711500710949

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm



Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 15W/10 1SL/25

