



# MASTER TL-E Circular Super 80

## TL-E 32W/830 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Product data

General Information		LLMF 8000 h Rated	
Cap-Base	G10Q [ G10q]		73 %
Life to 50% Failures (Nom)	13000 h	<b>Operating and Electrical</b>	
LSF 2000 h Rated	98 %	Power (Nom)	32.0 W
LSF 4000 h Rated	77 %	Lamp Current (Nom)	0.450 A
LSF 6000 h Rated	60 %	Voltage (Nom)	81 V
LSF 8000 h Rated	45 %	<b>Temperature</b>	
<b>Light Technical</b>		Design Temperature (Nom)	25 °C
Color Code	830 [ CCT of 3000K]	<b>Controls and Dimming</b>	
Luminous Flux (Nom)	2375 lm	Dimmable	Yes
Luminous Flux (Rated) (Nom)	2375 lm	<b>Approval and Application</b>	
Color Designation	Warm White (WW)	Energy Efficiency Label (EEL)	A
Correlated Color Temperature (Nom)	3000 K	Mercury (Hg) Content (Nom)	8 mg
Luminous Efficacy (rated) (Nom)	74 lm/W	Energy Consumption kWh/1000 h	35 kWh
Color Rendering Index (Nom)	80	<b>Product Data</b>	
LLMF 2000 h Rated	84 %	Full product code	871150055967800
LLMF 4000 h Rated	79 %		
LLMF 6000 h Rated	75 %		


# MASTER TL-E Circular Super 80

Order product name	TL-E 32W/830 1CT/20
EAN/UPC - Product	8711500559678
Order code	928026383074
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

Material Nr. (12NC)	928026383074
Net Weight (Piece)	0.180 kg
ILCOS Code	FSC-32/30/1B-E-G10q-29/299

## Warnings and Safety

## Dimensional drawing





TL-E 32W/830

## Product

TL-E 32W/830 1CT/20

## Photometric data



LDPO\_TL-E8\_830-Spectral power distribution Colour

