



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL-D 18W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Product data

General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		59 V
Main Application	Insect traps	Approval and Application	
Life to 50% Failures (Nom)	13000 h	Mercury (Hg) Content (Nom)	5.0 mg
Useful Life (Nom)	9000 h	UV	
Light Technical		UV-B/UV-A (IEC)	0.2 %
Color Code	10	UV-A Radiation 100Hr (IEC)	5.0 W
Color Designation	Actinic	Product Data	
Chromaticity Coordinate X (Nom)	222	Full product code	871150026325440
Chromaticity Coordinate Y (Nom)	210	Order product name	Actinic BL TL-D 18W/10 1SL/25
UV Depreciation at 2000 h	8 %	EAN/UPC - Product	8711500263254
UV Depreciation at 5000 h	12 %	Order code	928048001003
UV Depreciation at 8000 h	16 %	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	25
Power (Rated) (Nom)	18 W	Material Nr. (12NC)	928048001003
Lamp Current (Nom)	0.36 A	Net Weight (Piece)	71.000 g

Actinic BL TL(-K)/TL-D(-K)



Warnings and Safety

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 18W/10 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-D 18W/10

Photometric data



Lightcolor /10

Lightcolor /10

